

# Lovibond® Colour Measurement Tintometer® Group



## TR 500 Spectrophotometer (1x8mm Aperture)



- Compact, Lightweight and Easy to use Sphere Spectrophotometer
- Designed for Fast, Accurate and Precise Colour Measurement
- On Screen Target Display Allows Positioning to be Perfect Every Time
- OnShade Software Included for FREE – Perfect for Detailed Data Analysis

货号: 403040

### Handheld and Portable

Weighing only 600 grams, the TR 500 is the perfect lightweight portable spectrophotometer. It's compact and ergonomic design offers easy one-handed operation, helping to prevent operator fatigue and enabling more measurements per hour. Offering the possibility of 5000 measurements with 8 hours battery life enables the TR 500 to be used anywhere on site for a prolonged period of time.

### Accuracy

Giving accurate and repeatable results is what the TR 500 does best. The on board camera based locator, enables the user to position the instrument accurately on the chosen sample with minimal contact. This feature dramatically minimize the chances of geometric metamerism.

### Aperture Options

Choosing the correct aperture size for your surface is extremely important for accurate measurement. This is why the TR 500 has three aperture options available in either 8mm, 4mm or 1x3mm. This choice of customised aperture helps to ensure the instrument is perfect for your measurement needs.

### Calibration

The calibration board supplied with every TR 500 incorporates a white tile and black calibration plate. This allows minimum and maximum readings to be checked every 24 hours.

### FREE Software

As standard, the TR 500 comes with a FREE PC software package. The OnShade software allows for a detailed data analysis which can then be shared or printed via the optional micro printer accessory.

### Suitable for Multiple Applications

The versatility of the TR 500 means its suitable for multiple applications and has the ability to report CIE Lab, XYZ, Yxy, LCh, CIE LUV, Hunter Lab colour spaces,  $\Delta E^*L^*a^*b^*$ ,  $\Delta E^*C^*h^\circ$ ,  $\Delta E^*uv$ ,  $\Delta E^*94$ ,  $\Delta E^*cmc(2:1)$ ,  $\Delta E^*cmc(1:1)$ ,  $\Delta E^*00$ ,  $\Delta E$  Hunter Colour Difference Formulas; and can be set to D65, A, C, D50, D55, D75, F2, F7 & F11 illuminants. In addition, the TR 500 can report a wide selection of other Colorimetric Indexes: WI (ASTM E313, CIE/ISO, AATCC, Hunter), YI (ASTM D1925, ASTM 313), TI (ASTM, E313, CIE/ISO), Metamerism Index (MI), Colour stain, Colour Fastness, Colour Strength and Opacity. This data can be seen as either Spectral Value/ Graph, Colorimetric Value, Colour Difference Value/ Graph, PASS/ FAIL Result, Colour Offset or Samples Chromaticity values.

## 行业

其他行业 | 化工行业 | 医药行业 | 油气 | 食品和饮料行业

## 应用

塑料 | 日用品 | 涂料 | 纺织品

光源寿命 5 years, more than 3 million measurements

观测者 2° / 10°

多语言操作界面 英文, 德文, 法文, 西班牙, 葡萄牙, 中文

尺寸 184 x 105 x 77 mm

## TR 500 Spectrophotometer (1x8mm Aperture)

The TR 500 is a cost effective handheld spectrophotometer with a high-end specification. The ergonomic design, flexibility and on screen target display makes it ideal for quality control in the lab, field or in the manufacturing plant. Available in either 8mm, 4mm or 1x3mm aperture, the TR 500 offers the flexibility to choose the right measurement size for your chosen surface.

## Technical Data

<b>Applicable Standard</b>	ASTM 313 ASTM D1925 ASTM E308
<b>颜色类型</b>	Opaque
<b>光学测量结构</b>	Reflect: di: 8°, de: 8° (diffused illumination, 8 degree viewing angle)
<b>积分球尺寸</b>	48 mm
<b>分光模式</b>	Concave Grating
<b>Sensor</b>	256 image Element Double Array CMOS Image Sensor
<b>重复性</b>	MAV/SCI: $\Delta E^* \leq 0.05$
<b>显示</b>	3.5 inch TFT colour LCD, Capacitive Touch Screen
<b>数据接口</b>	USB
<b>光谱间隔</b>	10 nm
<b>测量模式</b>	Single Measurement, Average Measurement
<b>外部存储器</b>	2000 Standards : 20000 Samples
<b>定位方式</b>	Camera View Finder Locating
<b>反射率量程</b>	0 - 200 %
<b>测量时间</b>	2.6 s
<b>测量孔径</b>	Customized Aperture: 8mm/4mm & 1x3mm
<b>镜面反射</b>	SCI & SCE
<b>电源</b>	Li-ion Battery
<b>色差测量</b>	$\Delta E^*_{ab}$ , $\Delta E^*_{uv}$ , $\Delta E^*_{94}$ , $\Delta E^*_{cmc}$ (2:1), $\Delta E^*_{cmc}$ (1:1), $\Delta E^*_{00v}$ , $\Delta E$ (Hunter)
<b>电池寿命</b>	5000 measurements with 8 hours
<b>其他颜色指数</b>	WI (ASTM E313, CIE/ISO, AATCC, Hunter) YI (ASTM D1925, ASTM 313, TI (ASTM E313, CIE/ISO) Metamerism Index MI, Staining Fastness, Colour Fastness, Colour Strength, Opacity
<b>显示数据</b>	Spectrogram/Values, Samples Chromaticity Values, Colour Difference Values/Graph, PASS/FAIL Result, Colour Offset
<b>仪器台间差</b>	MAV/SCI: $\Delta E^* \leq 0.2$
<b>光谱范围</b>	400 - 700 nm
<b>带宽</b>	10 nm
<b>照明体</b>	CIE Illuminant D65 CIE Illuminant A CIE Illuminant C CIE Illuminant D50 CIE Illuminant D55 CIE Illuminant D75 CIE Illuminant F1 CIE Illuminant F2 CIE Illuminant F3 CIE Illuminant F4 CIE Illuminant F5 CIE Illuminant F6 CIE Illuminant F7 CIE Illuminant F8 CIE Illuminant F9 CIE Illuminant F10 CIE Illuminant F11 CIE Illuminant F12
<b>便携性</b>	手提

## 标准配置文本

- TR 500 Sphere Spectrophotometer
- OnShade PC Software
- White and Black Calibration Board
- Dust Cover
- USB Cable
- External DC Power Supply
- USB Stick with User Manuals in English, French, German, Spanish, Portuguese and Chinese
- Sturdy Carrying Case

---

**Tintometer GmbH**

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
德国

**The Tintometer Limited**

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
英国

**Tintometer China**

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
中国

**Tintometer South East Asia**

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
马来西亚

**Tintometer Brazil**

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
巴西

**Tintometer Inc.**

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
美国

**Tintometer India Pvt. Ltd.**

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
印度

**Tintometer Spain**

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
西班牙