

# Lovibond® Water Testing Tintometer® Group



## ET730 Portable Floc Tester, 4 positions

Floc testers with continuously variable stirring speed for laboratory and field use



- Completely Portable - designed to be used on-site for fast results in the field
- 4 Positions with backlight for easy viewing
- Easy to use with adjustable timer and RPM functions

Part Number: 2419150

Floc Testers (also known as Jar Testers) are designed for a range of applications - such as testing the efficiency of flocculation or precipitation agents.

### Lightweight and Completely Portable

The compact design makes this the ideal device for anyone performing flocculations in the field. The structure is epoxy painted and tested to give to an excellent resistance to the attack of chemical agents and corrosion. The non-skid base keeps the beakers stable during operation.

### Universal Power Supply

The low energy (6W) power supply allows the instrument to be connected to all frequencies and voltages in the world (100-240V / 50-60Hz). The device can be connected to a traditional wall plug, or can be operated from a portable battery or from vehicle cigarette lighter port.

### Stirring Speed Control

User selectable choice of 20-40-50-100-200 rpm stirring speeds. The stirring speed is the same for each position. In addition, the stirring rods can be adjustable in height without the use of tools.

### Timer Function

The timer can be set for 1 - 30 minutes, or to continuous operation mode. When the timer expires, the instrument will automatically turn off, allowing for unattended operation of the device.

### Illuminated Backdrop

The center column between the jars is illuminated - making it easy to visually compare samples.

## Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Oil and Gas | Pharmaceutical Industry

## ET730 Portable Floc Tester, 4 positions

The Floc Tester ET 730 with 4 stirring points is designed primarily for mobile use.

## Technical Data

<b>Power Supply</b>	100 - 240 V / 50-60 Hz
<b>Timer</b>	0 - 30 minutes (continuous)
<b>Stirring Places</b>	4
<b>Stirring Speed Control</b>	20 - 40 - 50 - 100 - 200 revolutions per minute
<b>Compliance</b>	CE
<b>Dimensions</b>	12.6 x 9.84 x 9.84"

## Accessories

Title	Part Number
Bag for transport	419151
Measuring beaker, glass 1000 ml	419165
Measuring beaker, PP 1000 ml	419166

## Delivery Scope

- With 4 stirring units
- Regulator for rpm from 20 - 40 - 50 - 100 - 200 rpm
- Operation indicator lamp
- Separate switch for sample illumination
- Instruction manual
- Warranty information

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Germany

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

### Tintometer China

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brazil

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
USA

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies