

Lovibond® Colour Measurement Tintometer® Group



RT310 (0/45) 15 mm aperture

Conveniently Measure Colour On-The-Go



- Easy-To-Read, In-Built Graphical Display
- Pass/Fail Mode for up to 1,024 Standards with Tolerances / 2000 Samples
- 15 mm Measurement Area / 21.5 mm Target Window
- Identifies Variation in In-Coming Goods & Batches

Part Number: 400310

Convenient Colour Measurement

This instrument allows you to obtain absolute and differential measurements. It is ideal for situations where Quality Controllers may have different requirements and levels of skill but need to work together to share data and establish consistency across the supply chain. Reducing the colour approval cycle speeds time to market.

Easy To Read and Easy To Understand

The RT 300 features an easy-to-read graphical LCD display and a pass/fail mode that measures against up to 1,024 standards with tolerances that can be stored for easy pass/fail measurement. Regardless on how skilled you are, this feature is a fast way for you to evaluate the colour of an object against an established standard.

Saves Time, Wastage and Costs

Accurately measuring colour helps you identify any variation in incoming materials, production batches and more, before it's too late.

Flexibility in Presented Results

The wide colorimetric range meets a number of CIE certifications and includes CIE XYZ, CIE Yxy, CIE LAB, Hunter LAB, CIE LCH, CME, CIE94, Whiteness and Yellow. Furthermore, if you are looking for more flexibility in presentation, the RT 310 also provides an interface to RT Colour Software.

Enhanced Quality Software Control

The RT 300 series can be combined with the OnColor™ software package allowing you to download measurement data, analyse in detail and store indefinitely on a PC.

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Oil and Gas | Pharmaceutical Industry

Application

Coatings | Food and Beverage | Household Products | Medical and-Clinical Products | Plastics

RT310 (0/45) 15 mm aperture

This portable handheld (0/45) 15 mm aperture spectrophotometer is the most convenient way for you to measure colour, allowing you to obtain absolute and differential measurements in the lab, plant or field.

Technical Data

Applicable Standard	ASTM 313 ASTM D1925 ASTM D7843 ASTM E308
Colour Type	Transparent Translucent Opaque
Spectral Interval	10 nm - measured; 10nm - output
Measurement Range	0 tot 200 % reflectie
Measurement Time	Approx 2 seconds
Lamp Life	Approx 500,000 measurements
Storage Temperature	-4 to 122°F (-20° to 50°C)
Spectral Range	400 - 700 nm
Portability	Benchtop

Delivery Scope

- Sturdy Box Including
- Instrument
- Calibration box
- Universal power supply
- Instruction manual

Accessories

Title	Part Number
RT On-Colour Premium Software	400610
RT300/400/500 Benchtop Stand	400620
RT300/400/500 Lqd Cell Holder	400630
RT300/400/500 Powder Cell Holder	400640
RT V-Block Sample Holder	400660
RT300/400/500 Pellet Holder	400680

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies