

# Lovibond® Colour Measurement Tintometer® Group



## TG 268 Gloss Meter



- Handheld Gloss Meter Designed to Give Fast, Precise and Accurate Gloss Readings
- Three Measurement Angles of 20°, 60° and 85°
- Compare Data Quick and Easy With a Data Storage Capacity of Over 5000 Data Sets
- OnGloss Software Included for FREE – Perfect for Detailed Data Analysis

Ürün No: 403045

### Handheld and Portable

Weighing only 350 grams, the TG 268 is the perfect lightweight portable gloss meter. Its compact and ergonomic design offers easy one-handed operation, helping to prevent operator fatigue. Offering the possibility of 1,000 measurements with 8 hours battery life enables the TG 268 to be used anywhere on site for a prolonged period of time.

### Flexibility

The TG 268 offers the user high flexibility. With detector angles of 20°/ 60°/ 85° the TG 268 can measure low, medium and high gloss levels on a wide range of materials. To enhance flexibility even further, basic, statistical and continuous measurement modes are available to ensure the TG 268 can be set perfectly to the user's needs.

### Calibration

Every TG 268 is supplied with a calibration plate and easy to use on screen calibration guide making the whole procedure fast and simple for the user.

### FREE Software

As standard, the TG 268 comes with a FREE PC software package. The OnGloss software allows for a detailed data analysis which can then be shared or printed via the optional micro printer accessory.

### Suitable for Multiple Standards

The TG 268 is able to support the following standard gloss levels: ASTM D523; ASTM C584; ASTM D2457; BS3900 D5; DIN 67530; DIN EN ISO 2813; EN ISO 7668 and JIS Z 8741.

### Uygulama

Ev Ürünleri | Kaplamalar | Plastikler | Tekstiller

### TG 268 Gloss Meter

The TG 268 is a cost-effective handheld gloss meter with a high-end specification. The ergonomic design, flexibility and intuitive touch screen technology makes the TG 268 equal in sophistication to any handheld gloss meter on the market. The meter comes with the ability to select 20°, 60° and 85° measurement angles and the choice of multiple measuring modes making it ideal for quality control in the production process of many industries.

## Teknik Veri

<b>Renk Türü</b>	Opaque
<b>Ekran</b>	TFT 3.5 inch, capacitive touch screen
<b>Arayüzler</b>	USB RS 232
<b>Ölçüm Aralığı</b>	0 - 10 parlaklık birimi, tekrarlanabilirlik $\pm 0,1$ parlaklık birimi, tekrarlanabilirlik $\pm 0,2$ parlaklık birimi 10 - 100 parlaklık birimi, tekrarlanabilirlik $\pm 0,2$ parlaklık birimi, tekrar üretilebilirlik $\pm 0,5$ parlaklık birimi 100-2000 parlaklık birimi, tekrarlanabilirlik $\pm 0,2$ parlaklık birimi, tekrarlanabilirlik $\pm 0,5$ parlaklık birimi
<b>Measuring Angle</b>	20° / 60° / 85°
<b>Ölçüm Alanı</b>	20°: 10 x10 ; 60°: 9 x15 ; 85°: 5 x 36
<b>Ölçüm Aralığı</b>	20°: 0 - 2000 GU ; 60°: 0 - 1000 GU ; 85°: 0 - 160 GU
<b>Division Value</b>	0.1 GU
<b>Dahali Depolama</b>	Basic Mode: 1000 ; Statistical Mode: 5000 ; Continuous Mode: 5000
<b>Ölçüm Süresi</b>	1.0 s
<b>Güç Kaynağı</b>	3200 mAh Li-ion Battery
<b>Pil Ömrü</b>	> 1000 times (within 8 hours)
<b>Taşınabilirlik</b>	Taşınabilir
<b>Diller Kullanıcı Arabirimi</b>	İngilizce
<b>Boyutlar</b>	160 x 90 x 75 mm

## Teslimat Kapsam Metni

- TG 268 Handheld Gloss Meter
- OnGloss Software (PC)
- Calibration Plate
- USB Cable
- External DC Power Supply
- USB Stick with User Manuals in English, French, German, Spanish, Portuguese and Chinese
- Sturdy Carrying Case

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Almanya

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
Birleşik Krallık

### Tintometer China

Room 1001, China Life Tower  
16 Chaoyangmenwai Avenue,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 App. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
Çin

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malezya

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brezilya

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
Amerika Birleşik Devletleri

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
Hindistan

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
İspanya