


# Lovibond® Colour Measurement Tintometer® Group



## TG 60 Gloss Meter



- Handheld Semi-Gloss Meter Designed to Give Fast, Precise and Accurate Gloss Readings
- Large 3.5 Inch Touch Screen with High Resolution and Full View Display
- Compare Data Quick and Easy with a Data Storage Capacity of 1000 Data Sets
- OnGloss Software Included for FREE – Perfect for Detailed Data Analysis

Part Number: 403050

### Handheld and Portable

Weighing only 350 grams, the TG 60 is the perfect lightweight portable semi-gloss meter. Its compact and ergonomic design offers easy one-handed operation, helping to prevent operator fatigue. Offering the possibility of 1,000 measurements with 8 hours battery life enables the TG 60 to be used anywhere on site for a prolonged period of time.

### Calibration

Every TG 60 is supplied with a calibration plate and easy to use on screen calibration guide making the whole procedure fast and simple for the user.

### FREE Software

As standard, the TG 60 comes with a FREE PC software package. The OnGloss software allows for a detailed data analysis which can then be shared or printed via the optional micro printer accessory.

### Suitable for Multiple Standards

The TG 60 is able to support the following standard gloss levels: ASTM D523; ASTM C584; ASTM D2457; BS3900 D5; DIN 67530; DIN EN ISO 2813; EN ISO 7668 and JIS Z 8741.

### Application

Coatings | Household Products | Plastics | Textiles

### TG 60 Gloss Meter

The TG 60 is an entry-level handheld semi-gloss meter with a high end specification. The ergonomic design, flexibility and intuitive touch screen technology makes the TG 60 equal in sophistication to any handheld semi-gloss meter on the market. Using the standard reference angle of 60° the TG 60 is the ideal choice for general gloss measurements.

### Technical Data

<b>Color Type</b>	Opaque
<b>Display</b>	TFT 3.5 inch, capacitive touch screen
<b>Interfaces</b>	USB RS 232
<b>Measurement Range</b>	0 - 10 gloss units, reproducibility $\pm 0.1$ gloss units, reproducibility $\pm 0.2$ gloss units 10 - 100 gloss units, reproducibility $\pm 0.2$ gloss units, reproducibility $\pm 0.5$ gloss units 100 - 300 gloss units, reproducibility $\pm 0.2\%$ gloss units, reproducibility $\pm 0.5\%$ gloss units
<b>Measuring Angle</b>	60°
<b>Measuring Area</b>	9 x 15
<b>Measuring Range</b>	0 - 300 GU
<b>Division Value</b>	0.1 GU
<b>Internal Storage</b>	Basic Mode: 1000
<b>Measurement Time</b>	0.5 s
<b>Power Supply</b>	3200 mAh Li-ion Battery

<b>Battery Life Time</b>	> 1000 times (within 8 hours)
<b>Portability</b>	Portable
<b>Languages User Interface</b>	English
<b>Dimensions</b>	160 x 90 x 75 mm

## Delivery Scope

- TG 60 Handheld Semi-Gloss Meter
- OnGloss Software (PC)
- Calibration Plate
- USB Cable
- External DC Power Supply
- USB Stick with User Manuals in English, French, German, Spanish, Portuguese and Chinese
- Sturdy Carrying Case

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Germany

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

### Tintometer China

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebu Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brazil

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
USA

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain