

Lovibond® Colour Measurement Tintometer® Group



AF509C for Marine Diesel Fuel Type F76

Kit for Visual Color Grading of Type F76 Marine Diesel Fuels according to ASTM Color



- Fast, Economical & Portable Visual Matching
- Two-Field Vision for Accurate Results
- Ability to Guarantee Constant Lighting Conditions

Part Number: 415090

Quick, On-site Color Measurement

This special kit enables you to quickly measure the color of type F76 marine diesel fuels according to a limited range of the ASTM Color Scale. It is designed to ensure that the correct fuel is used in motor vessels running with type F76 diesel, thereby avoiding errors in fuel use that can result in expensive corrective maintenance. The test is based on a direct color match between the sample and a test disc containing ASTM Color standards, enabling you to accept or reject the diesel fuel in a matter of minutes.

Easy Determination

The Lovibond® AF 509/C includes a test disc containing a limited range of ASTM Color standards (1 - 5 units as opposed to the full range of 0.5 - 8 units). This is sufficient for this purpose since type F76 fuel has a target color of 3.5 ASTM Color and reduces the options for you to choose from.

Fast, Economical & Portable Visual Matching

The Comparator 2000+ is a flexible, modular system for Visual Color Grading. Using a suitable comparator instrument and glass disc, you can quickly visually match the sample directly against the calibrated, color stable glass standards.

Two-Field Vision for Accurate Results

Lovibond® comparator instruments include an integrated prism which causes the sample and comparison fields to overlap, allowing enhanced color discrimination and matching. The prism is ultrasonically sealed to prevent contamination of the optics. Each individually graded glass standard represents a discrete step on the measurement range (as opposed to a continuous graduation), aiding color discrimination and allowing great accuracy of results.

Ability to Guarantee Constant Lighting Conditions

An optional item for the Comparator 2000+ is the Daylight 2000 Lighting Unit. This is a standardized light source which guarantees you a constant lighting condition for accurate color grading. This is particularly useful when the sample is very pale in color. By using a Lovibond® lighting unit, you can confident of uniform lighting conditions for color matching, 24 hours a day and irrespective of ambient lighting.

Extended Shelf Life

The unique feature of Lovibond® test discs is that they incorporate colored glass standards that are color stable and not affected by UV light or extreme environmental conditions.

Please note, we cannot guarantee compatibility of discontinued Lovibond® Comparator 1000 disks with the Lovibond® 2000+ Comparator.

Industry

Oil and Gas

Application

Petroleum Oils and Waxes

AF509C for Marine Diesel Fuel Type F76

The Comparator 2000+ is an easy-to-use, entry level color measurement system that compares the color of the sample directly

against the color of glass in a disc. All you need to do is rotate the disc to get the closest result to the scale.

Technical Data

Applicable Standard ASTM D1500
ASTM D6045
ISO 2049

Color Type Transparent

Portability Portable

Delivery Scope

- Sturdy Case Including
- 1 x Lovibond 2000+ Comparator
- 1 x 4/81 ASTM Diesel Fuel Disc
Precalibrated to 1, 2, 3, 4.5, 4, 4.5, 5
- 2 x W680.OG.33mm Cell
- 1 x Kit Instructions

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebu Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies