

Lovibond® Colour Measurement Tintometer® Group



TR 500 Spectrophotometer (1x8mm Aperture)



- Compact, Lightweight and Easy to use Sphere Spectrophotometer
- Designed for Fast, Accurate and Precise Colour Measurement
- On Screen Target Display Allows Positioning to be Perfect Every Time
- OnShade Software Included for FREE – Perfect for Detailed Data Analysis

Referencia No: 403040

Handheld and Portable

Weighing only 600 grams, the TR 500 is the perfect lightweight portable spectrophotometer. It's compact and ergonomic design offers easy one-handed operation, helping to prevent operator fatigue and enabling more measurements per hour. Offering the possibility of 5000 measurements with 8 hours battery life enables the TR 500 to be used anywhere on site for a prolonged period of time.

Accuracy

Giving accurate and repeatable results is what the TR 500 does best. The on board camera based locator, enables the user to position the instrument accurately on the chosen sample with minimal contact. This feature dramatically minimize the chances of geometric metamerism.

Aperture Options

Choosing the correct aperture size for your surface is extremely important for accurate measurement. This is why the TR 500 has three aperture options available in either 8mm, 4mm or 1x3mm. This choice of customised aperture helps to ensure the instrument is perfect for your measurement needs.

Calibration

The calibration board supplied with every TR 500 incorporates a white tile and black calibration plate. This allows minimum and maximum readings to be checked every 24 hours.

FREE Software

As standard, the TR 500 comes with a FREE PC software package. The OnShade software allows for a detailed data analysis which can then be shared or printed via the optional micro printer accessory.

Suitable for Multiple Applications

The versatility of the TR 500 means its suitable for multiple applications and has the ability to report CIE Lab, XYZ, Yxy, LCh, CIE LUV, Hunter Lab colour spaces, $\Delta E^*L^*a^*b^*$, $\Delta E^*C^*h^\circ$, ΔE^*uv , ΔE^*94 , $\Delta E^*cmc(2:1)$, $\Delta E^*cmc(1:1)$, ΔE^*00 , ΔE Hunter Colour Difference Formulas; and can be set to D65, A, C, D50, D55, D75, F2, F7 & F11 illuminants. In addition, the TR 500 can report a wide selection of other Colorimetric Indexes: WI (ASTM E313, CIE/ISO, AATCC, Hunter), YI (ASTM D1925, ASTM 313), TI (ASTM, E313, CIE/ISO), Metamerism Index (MI), Colour stain, Colour Fastness, Colour Strength and Opacity. This data can be seen as either Spectral Value/ Graph, Colorimetric Value, Colour Difference Value/ Graph, PASS/ FAIL Result, Colour Offset or Samples Chromaticity values.

Industria

Gas y petróleo | Industria alimentaria | Industria farmacéutica | Industria química | Otras industrias

Aplicaciones

Plásticos | Productos para el hogar | Recubrimientos | Textiles

TR 500 Spectrophotometer (1x8mm Aperture)

The TR 500 is a cost effective handheld spectrophotometer with a high-end specification. The ergonomic design, flexibility and on screen target display makes it ideal for quality control in the lab, field or in the manufacturing plant. Available in either 8mm, 4mm or 1x3mm aperture, the TR 500 offers the flexibility to choose the right measurement size for your chosen surface.

Datos técnicos

| | |
|-----------------------------------|--|
| Applicable Standard | ASTM 313 ASTM D1925 ASTM E308 |
| Colour Type | Opaque |
| Optical Geometry | Reflect: di: 8°, de: 8° (diffused illumination, 8 degree viewing angle) |
| Integrating Sphere Size | 48 mm |
| Spectrophotometric Mode | Concave Grating |
| Sensor | 256 image Element Double Array CMOS Image Sensor |
| Repetibilidad | MAV/SCI: $\Delta E^* \leq 0.05$ |
| Display | 3.5 inch TFT colour LCD, Capacitive Touch Screen |
| Interfaces | USB |
| Intervalo espectral | 10 nm |
| Measurement Mode | Single Measurement, Average Measurement |
| Almacenamiento externo | 2000 Standards : 20000 Samples |
| Location Method | Camera View Finder Locating |
| Measured Reflectance Range | 0 - 200 % |
| Tiempo de medición | 2.6 s |
| Measuring Aperture | Customized Aperture: 8mm/4mm & 1x3mm |
| Specular Component | SCI & SCE |
| Alimentación eléctrica | Li-ion Battery |
| Colour Difference Formular | ΔE^*_{ab} , ΔE^*_{uv} , ΔE^*_{94} , ΔE^*_{cmc} (2:1), ΔE^*_{cmc} (1:1), ΔE^*_{00v} , ΔE (Hunter) |
| Vida de la batería | 5000 measurements with 8 hours |
| Other Colorimetric Index | WI (ASTM E313, CIE/ISO, AATCC, Hunter) YI (ASTM D1925, ASTM 313, TI (ASTM E313, CIE/ISO) Metamerism Index MI, Staining Fastness, Colour Fastness, Colour Strength, Opacity |
| Displayed Data | Spectrogram/Values, Samples Chromaticity Values, Colour Difference Values/Graph, PASS/FAIL Result, Colour Offset |
| Acuerdo inter-instrumentos | MAV/SCI: $\Delta E^* \leq 0.2$ |
| Campos espectrales | 400 - 700 nm |
| Ancho de banda | 10 nm |
| Fuentes de luz | CIE Illuminant D65 CIE Illuminant A CIE Illuminant C CIE Illuminant D50 CIE Illuminant D55 CIE Illuminant D75 CIE Illuminant F1 CIE Illuminant F2 CIE Illuminant F3 CIE Illuminant F4 CIE Illuminant F5 CIE Illuminant F6 CIE Illuminant F7 CIE Illuminant F8 |

CIE Illuminant F9
CIE Illuminant F10
CIE Illuminant F11
CIE Illuminant F12

| | |
|------------------------------------|--|
| Portabilidad | Portátil |
| Illuminant Life Span | 5 years, more than 3 million measurements |
| Observador | 2° / 10° |
| Idiomas Interfaz de usuario | Inglés, Alemán, Francés, Español, Portugués, Chino |
| Medidas | 184 x 105 x 77 mm |

Volumen de suministro

- TR 500 Sphere Spectrophotometer
- OnShade PC Software
- White and Black Calibration Board
- Dust Cover
- USB Cable
- External DC Power Supply
- USB Stick with User Manuals in English, French, German, Spanish, Portuguese and Chinese
- Sturdy Carrying Case

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Alemania

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
Reino Unido

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malasia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brasil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
Estados Unidos de América

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
España