


Lovibond® Colour Measurement Tintometer® Group



TG 268 Gloss Meter



- Handheld Gloss Meter Designed to Give Fast, Precise and Accurate Gloss Readings
- Three Measurement Angles of 20°, 60° and 85°
- Compare Data Quick and Easy With a Data Storage Capacity of Over 5000 Data Sets
- OnGloss Software Included for FREE – Perfect for Detailed Data Analysis

Code: 403045

Handheld and Portable

Weighing only 350 grams, the TG 268 is the perfect lightweight portable gloss meter. Its compact and ergonomic design offers easy one-handed operation, helping to prevent operator fatigue. Offering the possibility of 1,000 measurements with 8 hours battery life enables the TG 268 to be used anywhere on site for a prolonged period of time.

Flexibility

The TG 268 offers the user high flexibility. With detector angles of 20°/ 60°/ 85° the TG 268 can measure low, medium and high gloss levels on a wide range of materials. To enhance flexibility even further, basic, statistical and continuous measurement modes are available to ensure the TG 268 can be set perfectly to the user's needs.

Calibration

Every TG 268 is supplied with a calibration plate and easy to use on screen calibration guide making the whole procedure fast and simple for the user.

FREE Software

As standard, the TG 268 comes with a FREE PC software package. The OnGloss software allows for a detailed data analysis which can then be shared or printed via the optional micro printer accessory.

Suitable for Multiple Standards

The TG 268 is able to support the following standard gloss levels: ASTM D523; ASTM C584; ASTM D2457; BS3900 D5; DIN 67530; DIN EN ISO 2813; EN ISO 7668 and JIS Z 8741.

Applications

Matières plastiques | Produits ménagers | Revêtements | Textiles

TG 268 Gloss Meter

The TG 268 is a cost-effective handheld gloss meter with a high-end specification. The ergonomic design, flexibility and intuitive touch screen technology makes the TG 268 equal in sophistication to any handheld gloss meter on the market. The meter comes with the ability to select 20°, 60° and 85° measurement angles and the choice of multiple measuring modes making it ideal for quality control in the production process of many industries.

Fiche technique

Type de Couleur	Opaque
Display	TFT 3.5 inch, capacitive touch screen
Interfaces	USB RS 232
Plages de mesure	0 - 10 unités de brillance, reproductibilité $\pm 0,1$ unité de brillance, reproductibilité $\pm 0,2$ unité de brillance 10 - 100 unités de brillance, reproductibilité $\pm 0,2$ unité de brillance, reproductibilité $\pm 0,5$ unité de brillance 100 - 2000 unités de brillance, reproductibilité $\pm 0,2\%$ unités de brillance, reproductibilité $\pm 0,5\%$ unités de brillance
Measuring Angle	20° / 60° / 85°
Zone de Mesure	20°: 10 x10 ; 60°: 9 x15 ; 85°: 5 x 36
Gamme de mesure	20°: 0 - 2000 GU ; 60°: 0 - 1000 GU ; 85°: 0 - 160 GU
Division Value	0.1 GU
Stockage interne	Basic Mode: 1000 ; Statistical Mode: 5000 ; Continuous Mode: 5000
Heure de la mesure	1.0 s
Alimentation	3200 mAh Li-ion Battery
Durée de vie batterie	> 1000 times (within 8 hours)
Portabilité	Portable
Langues interface d'utilisateur	Anglais
Dimensions	160 x 90 x 75 mm

Contenu de livraison

- TG 268 Handheld Gloss Meter
- OnGloss Software (PC)
- Calibration Plate
- USB Cable
- External DC Power Supply
- USB Stick with User Manuals in English, French, German, Spanish, Portuguese and Chinese
- Sturdy Carrying Case

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Allemagne

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
Royaume-Uni

Tintometer China

Room 1001, China Life Tower
16 Chaoyangmenwai Avenue,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 App. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
Chine

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaisie

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brésil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
États-Unis

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
Inde

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Espagne

Sous réserve de modifications techniques

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies