

# Lovibond® Water Testing Tintometer® Group



## SD20 ORP



- Transparent lid for easy maintenance and storage
- Ideal lid design for a stable stand
- Display colours & symbols for easy use
- New multi-parameter models for individual measurement requirements

Ürün No: 720020

### Sanayi

Belediyeler | Deniz Sanayi | Diğer Sanayiler | Halka Açık Havuz | Havuz Hizmetleri

### SD20 ORP

With its waterproof housing, the Pocket Tester is ideal for regular checks in industrial plants or swimming pools.

Plus, the transparent lid not only provides a secure stand for the Pocket Tester in daily use, but also makes it easier to maintain the electrodes. A three-colour LED lighting system - blue, green and red - and new display icons make the tester easy to use and intuitive to operate. The use of energy saving LEDs and 4 x AAA batteries greatly extends the life of the new Pocket Tester range to up to 2000 hours.

With the included lanyard, each SD Series tester can be worn comfortably around the neck or attached to a pocket, waistband or belt with the clip on the head of the tester, allowing it to be taken anywhere without tiring the hands.

### Ölçüm Aralığı

Test Name	Ölçüm Aralığı
ORP	-1000 - 1000 mV
Temperature	0 - 50 °C

### Teknik Veri

<b>Doğruluk</b>	mV: $\pm 0.2$ % FS Temperature: $\pm 0.5$ °C
<b>Ekran</b>	3 coloured backlit LCD (blue: measurement, green: calibration, red: alarm)
<b>Auto – OFF</b>	Evet
<b>Kalibrasyon</b>	1 nokta ayarı +/- 150 mV ayarlanabilen ORP değeri
<b>Güç Kaynağı</b>	4 mikro pil (AAA)
<b>Pil Ömrü</b>	> 350 saat (sürekli çalışma, aydınlatma kapalı), ekranda pil durumu göstergesi
<b>Taşınabilirlik</b>	Taşınabilir
<b>Kararlılık</b>	ORP: 1 mV
<b>Resolution Temperature</b>	0.1 °C
<b>Calibration Points</b>	1
<b>Buffer Auto Recognition</b>	+ 470 mV (25 °C), Pt   Ag/AgCl (3 M KCl)
<b>Calibration Indicator</b>	Hayır
<b>Stability Indicator</b>	Evet
<b>Auto-Hold Function</b>	Evet
<b>Alarm Limits</b>	Evet
<b>Uygunluk</b>	CE
<b>Boyutlar</b>	40 x 40 x 180 mm
<b>Ambalajlı Ağırlık</b>	268 g

# Teslimat Kapsam Metni

- Tester incl. electrode
- 4 AAA batteries
- Lanyard
- Storage box
- 3 M KCl Storage Solution for pH/ORP
- Multilingual instruction manual
- Certificate of compliance
- Warranty declaration

## Aksesuarlar

Başlık	Ürün No
Mikro pil (AAA), 4'lü set	1950026
Redox kalibrasyon çözeltisi, 470 mV, 100 ml	195070
Ölçü kabı, 100 ml	384801
VE suyu	461275
SD20 ORP için yedek elektrot	720025
PH / ORP için 3 M KCl Depolama Solüsyonu, 25 ml	726402
PH / ORP için 3 M KCl Depolama Solüsyonu, 100 ml	726404

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Almanya

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
Birleşik Krallık

### Tintometer China

Room 1001, China Life Tower  
16 Chaoyangmenwai Avenue,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 App. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
Çin

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malezya

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brezilya

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
Amerika Birleşik Devletleri

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
Hindistan

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
İspanya