

Lovibond® Water Testing

Tintometer® Group



SD315 Oxi, Dissolved Oxygen Meter, Set 2

Waterproof Hand-held Meters for the determination of pH/Redox/Temperature Conductivity, TDS, Salinity, Temperature

Dissolved oxygen (O₂) O₂ -Concentration O₂ -Saturation Temperature



- Rugged, water resistant (IP 67)
- PC interface (USB / serial or analog)
- Automatic buffer detection (SD 300 pH)
- Data logger and alarm function (min./ max.)

Part Number: 724690

No polarization

The well-known Clark oxygen sensor allows immediate measurement without polarization time.

Versatile

The SD 315 Oxi is aimed at industry, laboratories and urban facilities, such as sewage treatment or water works.

Data management

A data logger and the corresponding logger software ensure simplified processing of the data obtained.

To ensure that this works under all visual conditions, the device is delivered with a backlit display.

housing

The protective armor not only guarantees a secure grip but also protection against fall damage.

The stand attached to the back of the housing can also be used as a hanger or belt clip.

Alarm

The integrated alarm alerts you if the measured value deviates once from the predefined values.

Auto-Hold

The auto-hold function makes it easy to read the measured values.

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Power and Energy

SD315 Oxi, Dissolved Oxygen Meter, Set 2

Portable handheld instrument for the determination of dissolved oxygen. It's reliable, rugged, and ideal for instant measurements with no time-consuming polarization time, thanks to the Clark oxygen sensor.

Measuring Range

Test Name	Measuring Range
Oxygen	0 - 70 mg/L O ₂
Oxygen	0 - 600 %
Temperature	0 - 50 °C

Technical Data

Display	Backlit LCD
Data Logger	Manual Logger: 1000 data sets (single value by keystroke). Auto. Logger: 10000 data sets (cyclic, time interval: 1 - 3600 s)
Power Supply	2 AAA batteries Micro-USB
Portability	Portable
Compliance	CE
Languages User Interface	German, English, French, Spanish, Italian, Portuguese, Dutch, Chinese
Dimensions	3.86 x 1.46 x 6.46"

Delivery Scope

- Instrument in protective armouring including electrode holder
- Batteries
- Oxygen sensor with 10 m cable
- Elektrolyte solution (KOH) 100 ml
- Calibration bottle with sponge
- 2 pcs. spare membrane heads
- Instruction manual
- Warranty information

Accessories

Title	Part Number
KOH 100, Spare Electrolyte, 100ml for SD310 Oxi	19801130
Oxygen sensor for SD310 / SD315 Oxi with 2m cable, Platinum cathode/Lead anode	19805050
Oxygen sensor for SD310 / SD315 Oxi with 10m cable, Platinum cathode/Lead anode	19805051
Oxygen sensor for SD310 / SD315 Oxi with 30m cable, Platinum cathode/Lead anode	19805052
Protection cap for Oxygen sensor SD 310 / SD 315 Oxi for depth measurement (PVC)	19805055
Protection cap for Oxygen sensor SD310 / SD315 Oxi for depth measurement (brass)	19805056
Bottle for storage and calibration	19805057
USB cable, for connection to a computer for SD300/SD305	724620
GSOFT 3050 Windows-Software with logger for SD300 / SD305 series	724625
Service Set for Oxygen sensor SD300 / SD315 Oxi	724670
Case incl. foam for SD 305 series	725070

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies