

# Lovibond® Water Testing

## Tintometer® Group



## SD325 Con, Conductivity Meter, Set 2

Waterproof Hand-held Meters for the determination of pH/Redox/Temperature Conductivity, TDS, Salinity, Temperature

Dissolved oxygen (O<sub>2</sub>) O<sub>2</sub> -Concentration O<sub>2</sub> -Saturation Temperature



- Rugged, water resistant (IP 67)
- PC interface (USB / serial or analog)
- Automatic buffer detection (SD 300 pH)
- Data logger and alarm function (min./max.)

Part Number: 724750

### User-friendly operation

The comfortable operation is completed by a large, backlit display. So you have the measurement results directly in view in every situation.

### Technically advanced

Datalogger, automatic temperature compensation and buffer detection are further features of the SD 325 Con.

### Data management

Data collected by the data logger can be transferred to the computer via USB interface (serial or analogue).

### Housing

The protective armor not only guarantees a secure grip but also protection against fall damage. The stand attached to the back of the housing can also be used as a hanger or belt clip.

### Variable equipment

Depending on the measuring range, three conductivity measuring cells with innovative 2 or 4-pole technology are available.

### Additional equipment

Battery and electrode status indication, battery replacement display, auto-off, auto-hold, min./max. Value memory are mandatory functions.

### Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Power and Energy

### SD325 Con, Conductivity Meter, Set 2

Robust, waterproof (IP67) and portable handheld meter for measuring conductivity, TDS, salinity and temperature. Ease of use and protective arming guarantee safe working, even in extreme environmental conditions.

### Measuring Range

Test Name	Measuring Range
Conductivity	0 - 1000 mS/cm
Salinity	0 - 70 g/kg
TDS	0 - 5000 mg/L
Temperature	-5 - 100 °C

## Technical Data

<b>Display</b>	Backlit LCD
<b>Data Logger</b>	Manual Logger: 1000 data sets (single value by keystroke). Auto. Logger: 10000 data sets (cyclic, time interval: 1 - 3600 s)
<b>Power Supply</b>	2 AAA batteries Micro-USB
<b>Portability</b>	Portable
<b>Compliance</b>	CE RoHS WEEE
<b>Languages User Interface</b>	German, English, French, Spanish, Italian, Portuguese, Dutch, Chinese
<b>Dimensions</b>	5.04 x 6.46 x 1.46"

## Accessories

Title	Part Number
LC12 for SD320 / SD325 Con, up to 200 mS/cm	19805040
LC16 for SD320 / SD325 Con, up to 1000 mS/cm	19805045
LC10 Pure water conductivity cell for SD320 / SD325 with 1m cable	19805046
Calibration solution 1413 µS/cm, 500ml, traceable to NIST	722250
USB cable, for connection to a computer for SD300/SD305	724620
GSOFT 3050 Windows-Software with logger for SD300 / SD305 series	724625
Case incl. foam for SD 305 series	725070
Conductivity Solution (1413 µS/cm) - 90ml - traceable to NIST	726654
Conductivity Solution (12.88 mS/cm) - 90ml - traceable to NIST	726684

## Delivery Scope

- Instrument in protective armouring including electrode holder
- Batteries
- Conductivity cell LC 16 (measuring range 0-1000 mS/cm)
- Conductivity solutions (1413 µS/cm ; 12.88 mS/cm)
- Manual
- Warranty Information in case

### Tintometer GmbH

Lovibond® Water Testing  
Schleefstraße 8-12  
44287 Dortmund  
Tel.: +49 (0)231/94510-0  
sales@lovibond.com  
www.lovibond.com  
Germany

### The Tintometer Limited

Lovibond House  
Sun Rise Way  
Amesbury, SP4 7GR  
Tel.: +44 (0)1980 664800  
Fax: +44 (0)1980 625412  
sales@lovibond.uk  
www.lovibond.com  
UK

### Tintometer China

9F, SOHO II C.  
No.9 Guanghualu,  
Chaoyang District,  
Beijing, 100020  
Customer Care China Tel.: 4009021628  
Tel.: +86 10 85251111 Ext. 330  
Fax: +86 10 85251001  
chinaoffice@tintometer.com  
www.lovibond.com  
China

### Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,  
Lebuh Nilam 2, Bandar Bukit Tinggi,  
Klang, 41200, Selangor D.E  
Tel.: +60 (0)3 3325 2285/6  
Fax: +60 (0)3 3325 2287  
lovibond.asia@tintometer.com  
www.lovibond.com  
Malaysia

### Tintometer Brazil

Caixa Postal: 271  
CEP: 13201-970  
Jundiaí – SP  
Tel.: +55 (11) 3230-6410  
sales@lovibond.us  
www.lovibond.com.br  
Brazil

### Tintometer Inc.

6456 Parkland Drive  
Sarasota, FL 34243  
Tel: 941.756.6410  
Fax: 941.727.9654  
sales@lovibond.us  
www.lovibond.us  
USA

### Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2<sup>nd</sup>, 3<sup>rd</sup> & 4<sup>th</sup> Floor  
Sanathnagar Industrial Estate,  
Hyderabad, 500018  
Telangana  
Tel: +91 (0) 40 23883300  
Toll Free: 1 800 599 3891/ 3892  
indiaoffice@lovibond.in  
www.lovibondwater.in  
India

### Tintometer Spain

Postbox: 24047  
08080 Barcelona  
Tel.: +34 661 606 770  
sales@tintometer.es  
www.lovibond.com  
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies