

Lovibond® Water Testing

Tintometer® Group



SD325 Con, Conductivity Meter, Set 2

Waterproof Hand-held Meters for the determination of pH/Redox/Temperature Conductivity, TDS, Salinity, Temperature

Dissolved oxygen (O₂) O₂ -Concentration O₂ -Saturation Temperature



- Rugged, water resistant (IP 67)
- PC interface (USB / serial or analog)
- Automatic buffer detection (SD 300 pH)
- Data logger and alarm function (min./ max.)

Part Number: 724750

User-friendly operation

The comfortable operation is completed by a large, backlit display. So you have the measurement results directly in view in every situation.

Technically advanced

Datalogger, automatic temperature compensation and buffer detection are further features of the SD 325 Con.

Data management

Data collected by the data logger can be transferred to the computer via USB interface (serial or analogue).

Housing

The protective armor not only guarantees a secure grip but also protection against fall damage. The stand attached to the back of the housing can also be used as a hanger or belt clip.

Variable equipment

Depending on the measuring range, three conductivity measuring cells with innovative 2 or 4-pole technology are available.

Additional equipment

Battery and electrode status indication, battery replacement display, auto-off, auto-hold, min./max. Value memory are mandatory functions.

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Marine Industry | Municipalities | NGO | Oil and Gas | Pharmaceutical Industry | Power and Energy

SD325 Con, Conductivity Meter, Set 2

Robust, waterproof (IP67) and portable handheld meter for measuring conductivity, TDS, salinity and temperature. Ease of use and protective arming guarantee safe working, even in extreme environmental conditions.

Measuring Range

Test Name	Measuring Range
Conductivity	0 - 1000 mS/cm
Salinity	0 - 70 g/kg
TDS	0 - 5000 mg/L
Temperature	-5 - 100 °C

Technical Data

Display	Backlit LCD
Data Logger	Manual Logger: 1000 data sets (single value by keystroke). Auto. Logger: 10000 data sets (cyclic, time interval: 1 - 3600 s)
Power Supply	2 AAA batteries Micro-USB
Portability	Portable
Compliance	CE RoHS WEEE
Languages User Interface	German, English, French, Spanish, Italian, Portuguese, Dutch, Chinese
Dimensions	5.04 x 6.46 x 1.46"

Accessories

Title	Part Number
LC12 for SD320 / SD325 Con, up to 200 mS/cm	19805040
LC16 for SD320 / SD325 Con, up to 1000 mS/cm	19805045
LC10 Pure water conductivity cell for SD320 / SD325 with 1m cable	19805046
Calibration solution 1413 µS/cm, 500ml, traceable to NIST	722250
USB cable, for connection to a computer for SD300/SD305	724620
GSOFT 3050 Windows-Software with logger for SD300 / SD305 series	724625
Case incl. foam for SD 305 series	725070
Conductivity Solution (1413 µS/cm) - 90ml - traceable to NIST	726654
Conductivity Solution (12.88 mS/cm) - 90ml - traceable to NIST	726684

Delivery Scope

- Instrument in protective armouring including electrode holder
- Batteries
- Conductivity cell LC 16 (measuring range 0-1000 mS/cm)
- Conductivity solutions (1413 µS/cm ; 12.88 mS/cm)
- Manual
- Warranty Information in case

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies