

Lovibond® Water Testing Tintometer® Group



ET730 Portable Floc Tester, 4 positions

Floc testers with continuously variable stirring speed for laboratory and field use



- Completely Portable - designed to be used on-site for fast results in the field
- 4 Positions with backlight for easy viewing
- Easy to use with adjustable timer and RPM functions

Part Number: 2419150

Floc Testers (also known as Jar Testers) are designed for a range of applications - such as testing the efficiency of flocculation or precipitation agents.

Lightweight and Completely Portable

The compact design makes this the ideal device for anyone performing flocculations in the field. The structure is epoxy painted and tested to give to an excellent resistance to the attack of chemical agents and corrosion. The non-skid base keeps the beakers stable during operation.

Universal Power Supply

The low energy (6W) power supply allows the instrument to be connected to all frequencies and voltages in the world (100-240V / 50-60Hz). The device can be connected to a traditional wall plug, or can be operated from a portable battery or from vehicle cigarette lighter port.

Stirring Speed Control

User selectable choice of 20-40-50-100-200 rpm stirring speeds. The stirring speed is the same for each position. In addition, the stirring rods can be adjustable in height without the use of tools.

Timer Function

The timer can be set for 1 - 30 minutes, or to continuous operation mode. When the timer expires, the instrument will automatically turn off, allowing for unattended operation of the device.

Illuminated Backdrop

The center column between the jars is illuminated - making it easy to visually compare samples.

Industry

Chemical Industry | Food and Beverage Industry | Industries Others | Oil and Gas | Pharmaceutical Industry

ET730 Portable Floc Tester, 4 positions

The Floc Tester ET 730 with 4 stirring points is designed primarily for mobile use.

Technical Data

Power Supply	100 - 240 V / 50-60 Hz
Timer	0 - 30 minutes (continuous)
Stirring Places	4
Stirring Speed Control	20 - 40 - 50 - 100 - 200 revolutions per minute
Compliance	CE
Dimensions	12.6 x 9.84 x 9.84"

Accessories

Title	Part Number
Bag for transport	419151
Measuring beaker, glass 1000 ml	419165
Measuring beaker, PP 1000 ml	419166

Delivery Scope

- With 4 stirring units
- Regulator for rpm from 20 - 40 - 50 - 100 - 200 rpm
- Operation indicator lamp
- Separate switch for sample illumination
- Instruction manual
- Warranty information

Tintometer GmbH

Lovibond® Water Testing
Schleefstraße 8-12
44287 Dortmund
Tel.: +49 (0)231/94510-0
sales@lovibond.com
www.lovibond.com
Germany

The Tintometer Limited

Lovibond House
Sun Rise Way
Amesbury, SP4 7GR
Tel.: +44 (0)1980 664800
Fax: +44 (0)1980 625412
sales@lovibond.uk
www.lovibond.com
UK

Tintometer China

9F, SOHO II C.
No.9 Guanghualu,
Chaoyang District,
Beijing, 100020
Customer Care China Tel.: 4009021628
Tel.: +86 10 85251111 Ext. 330
Fax: +86 10 85251001
chinaoffice@tintometer.com
www.lovibond.com
China

Tintometer South East Asia

Unit B-3-12, BBT One Boulevard,
Lebuh Nilam 2, Bandar Bukit Tinggi,
Klang, 41200, Selangor D.E
Tel.: +60 (0)3 3325 2285/6
Fax: +60 (0)3 3325 2287
lovibond.asia@tintometer.com
www.lovibond.com
Malaysia

Tintometer Brazil

Caixa Postal: 271
CEP: 13201-970
Jundiaí – SP
Tel.: +55 (11) 3230-6410
sales@lovibond.us
www.lovibond.com.br
Brazil

Tintometer Inc.

6456 Parkland Drive
Sarasota, FL 34243
Tel: 941.756.6410
Fax: 941.727.9654
sales@lovibond.us
www.lovibond.us
USA

Tintometer India Pvt. Ltd.

Door No: 7-2-C-14, 2nd, 3rd & 4th Floor
Sanathnagar Industrial Estate,
Hyderabad, 500018
Telangana
Tel: +91 (0) 40 23883300
Toll Free: 1 800 599 3891/ 3892
indiaoffice@lovibond.in
www.lovibondwater.in
India

Tintometer Spain

Postbox: 24047
08080 Barcelona
Tel.: +34 661 606 770
sales@tintometer.es
www.lovibond.com
Spain

Technical changes without notice

Printed in Germany

Lovibond® and Tintometer® are Trademarks of the Tintometer Group of Companies